
Features

- 33 mm² PIN detector
- High sensitivity
- High shunt resistance
- Blue-green enhanced

Description

Blue-green enhanced square active area PIN photodiode with 33 mm² active area. Metal can type hermetic TO8 package with UV clear glass window.

Application



- Precision photometry
- Analytical instruments
- Medical equipment
- Fluorescence detector

RoHS

2002/95/EC


Absolute maximum ratings

Symbol	Parameter	Min	Max	Unit
T _{STG}	Storage temp	-55	125	°C
T _{OP}	Operating temp	-40	100	°C
V _{max}	Max reverse voltage		20	V
I _{PEAK}	Peak DC current		10	mA

Spectral response (23 °C)

Schematic

Electro-optical characteristics @ 23 °C




Symbol	Characteristic	Test Condition	Min	Typ	Max	Unit
	Active area		5694 x 5694			µm
	Active area		33			mm ²
I _D	Dark current	V _R = 5 V		0.6		nA
C	Capacitance	V _R = 0 V		400		pF
		V _R = 5 V		120		pF
	Responsivity	λ = 410 nm		0.22		A/W
		λ = 550 nm		0.37		A/W
t _r	Rise time	V _R = 0 V; λ = 410 nm; R _L = 50 Ω		400		ns
		V _R = 5 V; λ = 410 nm; R _L = 50 Ω		140		ns
	Shunt Resistance	V _R = 5 V; λ = 660 nm; R _L = 50 Ω		120		ns
		V _R = 5 mV		100		MΩ
	N.E.P.	V _R = 5 V; λ = 410 nm		6.3 E-14		W/√Hz
V _{BR}	Breakdown voltage	I _R = 2 µA	20	30		V

European, International Sales:


First Sensor AG
 Peter-Behrens-Strasse 15
 12459 Berlin
 Germany
 T +49 30 6399 2399
 F +49 30 639923-752
 sales.opto@first-sensor.com

USA:


First Sensor Inc.
 5700 Corsa Avenue #105
 Westlake Village
 CA 91362 USA
 T +1 818 706 3400
 F +1 818 889 7053
 sales.us@first-sensor.com

Quantum efficiency (23 °C)

Capacitance as fct of reverse bias (23 °C)

Dark current as fct of bias (23 °C)

Package dimension:

Small quantities: Foam pad, boxed (12 cm x 16.5 cm)

Handling:

Please refer to document "Instructions for handling and processing"

Disclaimer: Due to our strive for continuous improvement, specifications are subject to change within our PCN policy according to JESD46C.

European, International Sales:

 First Sensor AG
 Peter-Behrens-Strasse 15
 12459 Berlin
 Germany
 T +49 30 6399 2399
 F +49 30 639923-752
 sales.opto@first-sensor.com

USA:

 First Sensor Inc.
 5700 Corsa Avenue #105
 Westlake Village
 CA 91362 USA
 T +1 818 706 3400
 F +1 818 889 7053
 sales.us@first-sensor.com